

USOC XCELERATOR™ Jack

By Hubbell Premise Wiring  
Catalog # [HXJUB](#)

Telephone/Data, Jack, XCELERATOR, USOC 6-Position



Features

- RJ-25 USOC (RJ-25) Jack
- Exclusive 1-Punch Termination Reduces Termination Time by 75%
- Mating Cycles Exceed Industry Standard by Four Times
- Bulk Packaging Reduces Excess Waste on the Job

Performance

USOC

General

Catalog Number	HXJUB
Construction Material - Main Contact	Thermoplastic IDC: Phosphor Bronze with 100 Micro-Inch Tin Over Plating
Contact Point Material	Beryllium Copper with Gold Over Plating
EU RoHS Indicator	Yes
Item Type	Modular Jack
Material - Housing	High-impact thermoplastic (UL 94V-0)
Material - Mounting Hardware	Keystone
Operating Cycles	2000 Plug
Series	USOC
Size	0.86 (22) x 0.67 (17) x 1.29 (33)
Specifications	<ul style="list-style-type: none"><li>• Housing - High impact thermoplastic (UL 94 V-0)</li><li>• IDC Contact - Phosphor bronze with 100 micro-inch tin over nickel under plating</li><li>• Nose Contact - Beryllium copper with precious metal plating with nickel under-plating</li></ul>

Style	RJ-45 Jack
Temperature Rating	Max Continuous- 75° C, Minimum- -40° C Without Impact
UPC	662620824703

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	RJ45 Jack to IDC Punch Down
Contact Resistance	100 Ohm
Withstand Voltage	1,000 Vac @ 60 Hz

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• 6-Position USOC Compliant</li><li>• CSA Certified</li><li>• Mechanical TIA-568-C.2</li><li>• RoHS Compliant</li><li>• UL Listed 1863</li></ul>
----------------------	--

Logistics

Carton Quantity	25
Number of Pieces in Package	1

Product Assets

[Catalog Page - PREM B5 CatalogPage](#)  
[Catalog Page - PREM B05 Catalog Page](#)  
[Catalogs - Premise Wiring Catalog](#)  
[Literature - HDPJ High Density Jack Panels](#)  
[Specifications - HXJUB Specification Sheet French](#)  
[Specifications - HXJUB Specification Sheet English](#)