


USOC XCELERATOR™ Jack

By Hubbell Premise Wiring
Catalog # [HXJUR](#)

Telephone/Data, Jack, XCELERATOR, USOC 6-Position



Features

- RJ-25 USOC (RJ-25) Jack
- Exclusive 1-Punch Termination Reduces Termination Time by 75%
- Mating Cycles Exceed Industry Standard by Four Times
- Bulk Packaging Reduces Excess Waste on the Job

Performance

USOC

General

Catalog Number	HXJUR
Construction Material - Main Contact	Thermoplastic IDC: Phosphor Bronze with 100 Micro-Inch Tin Over Plating
Contact Point Material	Beryllium Copper with Gold Over Plating
EU RoHS Indicator	Yes
Item Type	Modular Jack
Material - Housing	High-impact thermoplastic (UL 94V-0)
Material - Mounting Hardware	Keystone
Operating Cycles	2000 Plug
Series	USOC
Size	0.86 (22) x 0.67 (17) x 1.29 (33)
Specifications	• Housing - High impact thermoplastic (UL 94 V-0) • IDC Contact - Phosphor bronze with 100 micro-inch tin over nickel under plating • Nose Contact - Beryllium copper with precious metal plating with nickel under-plating

Style	RJ-45 Jack
Temperature Rating	Max Continuous- 75° C, Minimum- -40° C Without Impact
UPC	662620824819

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	RJ45 Jack to IDC Punch Down
Contact Resistance	100 Ohm
Withstand Voltage	1,000 Vac @ 60 Hz

Certifications And Compliance

Industry Standard(s)	• 6-Position USOC Compliant • CSA Certified • Mechanical TIA-568 • RoHS Compliant • UL Listed 1864
----------------------	--

Logistics

Carton Quantity	25
Number of Pieces in Package	1

Product Assets

[Catalog Page - PREM B5 CatalogPage](#)
[Catalog Page - PREM B05 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Literature - HDPJ High Density Jack Panels](#)
[Specifications - HXJUR Specification Sheet French](#)
[Specifications - HXJUR Specification Sheet English](#)