

110 HDBaseT HDMI, VGAM, USB,
Analog Audio, RS232, IR, Auto-
Switching Extender

By Hubbell Premise Wiring
Catalog # [ISFHDT421BK](#)

110 HDBaseT HDMI, VGAM, USB, Analog Audio, RS232, IR, Auto-Switching Extender

Features

- USB
- Analog Audio
- RS232
- IR
- Auto-Switching Extender

Application

HDMI / USB / VGA

General

Catalog Number	ISFHDT421BK
Environmental Conditions	Indoor Dry Unless Protected by Additional Means
Mounting Type	Screw Mount
Series	ISFHD
Size	Standard Sized Product
Sub Brand	HDBT Modules
Temperature Rating	-40 Degrees C to 70 Degrees C
Type	Decorator Insert



UPC662620652412

Electrical Ratings

Contact Resistance	Nominal
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s)	TIA-NEMA
----------------------	----------

Logistics

Carton Quantity	40
-----------------	----

Product Assets

- [Catalog Page - PREM F04 Catalog Page](#)
- [Catalog Page - PREM F4 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - iStation HDBaseT 3.0 In-Wall HDMI Extender](#)
- [Specifications - ISFHDT421BK Specification Sheet French](#)
- [Specifications - ISFHDT421BK Specification Sheet English](#)
- [Specifications - PREMISE_ISFHDT421BK_spec](#)