

Cabinet Components, Power Strip,
19" Rack Mount, 10 Rear Outlets,
NEMA 5-15R Plug, 15A/120V, Flush,
Surge Protection

By Hubbell Premise Wiring
Catalog # [MCCPSS19](#)

Cabinet Power Strip Surge Protection, 19" Rack Mount , 10 Rear Outlets, NEMA 5-15R Plug, 15A/120V, Flush

Features

- 10 Rear Outlets
- NEMA 5-15R Plug
- 15A/120V
- Flush

Application

15A-120V

General

Catalog Number	MCCPSS19
Construction Material - Main	Steel
EU RoHS Indicator	Contact Manufacturer
Item Type	15A 125V
Material	Steel, Cold Rolled
Receptacle Type	NEMA 5-15R
Sensing Range	19 IN
Sub Brand	Power Distribution
Type	Rack Mount
UPC	662620787626



Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	120 V
Voltage Rating Description	120 V

Certifications And Compliance

Industry Standard(s)	UL
----------------------	----

Logistics

Carton Quantity	1
Pallet Quantity	96

Product Assets

[Catalog Page - PREM Q5 CatalogPage](#)
[Catalog Page - PREM Q05 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - ENTERPRISE AND DATA CENTER POWER SOLUTIONS Basic and Intelligent Power Distribution](#)
[Specifications - MCCPSS19 Specification Sheet English](#)
[Specifications - MCCPSS19 Specification Sheet French](#)