

Wiring Device Kellems, NetSelect,
Plate Frame, With Jacks, 6-Position
4-Conductor, Screw Terminal,
Electric Ivory

By Hubbell Premise Wiring
Catalog # [NS770I](#)



Wiring Device Kellems, NetSelect, Plate Frame, With Jacks, 6-Position 4-Conductor, Screw Terminal, Electric Ivory

Features

- Meets FCC part 68
- High impact-resistant thermoplastic frame

Application

Communications

General

Catalog Number	NS770I
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	1) 6-Position 4-Conductor Jack
Material - Mounting Hardware	Screw Mounting
Size	Standard
Specifications	Device Type - 6-Position, 4-Conductor
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Voice and Data
UPC	883778501692

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Screw Terminals
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - PREM T8 CatalogPage](#)
- [Catalog Page - PREM S13 Catalog Page](#)
- [Catalog Page - PREM V13 Catalog Page](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - Residential Catalog](#)
- [Specifications - NS770I Specification Sheet English](#)
- [Specifications - NS770I Specification Sheet French](#)