

Category 5e netSELECT™ Jack

By Hubbell Premise Wiring
Catalog # [NSJ5EW](#)



Features

- Easy To Terminate Angled Wiring Towers
- Exceeds TIA Category 5e Standards

Performance

TIA Cat 5e Component

General

Catalog Number	NSJ5EW
Construction Material - Main Contact	Thermoplastic IDC: Phosphor Bronze with 100 Micro-Inch Tin Over Plating
Contact Point Material	Beryllium Copper with Gold Over Plating
EU RoHS Indicator	Yes
Item Type	Modular Jack
Material - Housing	High-impact thermoplastic (UL 94V-0)
Material - Mounting Hardware	Screw Mounting
Operating Cycles	750+ Plug
Series	Cat 5e UTP
Size	0.86 (22) x 0.67 (17) x 1.29 (33)
Specifications	• Housing - High impact thermoplastic (UL 94 V-0) • IDC Contact - Phosphor bronze with 100 micro-inch tin over nickel under plating • Nose Contact - Beryllium copper with precious metal plating with nickel under-plating
Style	RJ-45 Jack
Temperature Rating	Max Continuous- 75° C, Minimum- -40° C Without Impact
UPC	883778500107

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	RJ45 Jack to IDC Punch Down
Contact Resistance	Per TIA
Insertion Loss	Per TIA
Withstand Voltage	1,000 Vac @ 60 Hz

Certifications And Compliance

Industry Standard(s)	• ANSI/TIA/EIA-568 Category 5e • UL 1863 - Communications-Circuit Accessory • IEC60512-99-002 POE Disconnection Endurance • UL 2043 - Suitable for Air-Handling Spaces • RoHS Compliant
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	25
Number of Pieces in Package	1
Pallet Quantity	9600

Product Assets

[Catalog Page - PREM V10 Catalog Page](#)
[Catalog Page - PREM S10 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - Residential Catalog](#)
[Specifications - NSJ5EW Specification Sheet English](#)
[Specifications - NSJ5EW Specification Sheet French](#)