

Net Select, Jack, Cat6, 8-Position,
Universal A/B, Office White, 24
Pack

By Hubbell Premise Wiring
Catalog # [NSJ6OW24](#)



Net Select, Jack, Cat6, 8-Position,Universal A/B, Office White, 24
Pack

Application

Telephone and Data Distribution Jack

General

Catalog Number	NSJ6OW24
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	1) Cat6 8-Position Universal A/B
Material - Mounting Hardware	Screw Mounting
Size	Standard Sized Product
Sub Brand	Copper Work Area
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	NEXTSPEED Category 6A, 6, 5e and USOC Jacks
UPC	883778507090

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	110 Punch Down
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s)	TIA
----------------------	-----

Logistics

Carton Quantity	4
-----------------	---

Product Assets

[Specifications - NSJ6OW24 Specification Sheet French](#)
[Specifications - NSJ6OW24 Specification Sheet English](#)