

USOC netSELECT™ Jack

By Hubbell Premise Wiring
Catalog # [NSJUW](#)

netSELECT™ RJ25 USOC modular jacks support various telephony applications. The innovative angled QuickLace™ termination towers provide ample room for lacing, accelerating the termination.

Features

- Easy To Terminate Angled Wiring Towers
- RJ25 USOC Telephone Jack

Performance

USOC

General

Catalog Number	NSJUW
Construction Material - Main Contact	Thermoplastic IDC: Phosphor Bronze with 100 Micro-Inch Tin Over Plating
Contact Point Material	Beryllium Copper with Gold Over Plating
EU RoHS Indicator	Yes
Item Type	Modular Jack
Material - Housing	High-impact thermoplastic (UL 94V-0)
Material - Mounting Hardware	Screw Mounting
Operating Cycles	750+ Plug
Series	USOC
Size	0.86 (22) x 0.67 (17) x 1.29 (33)
Specifications	<ul style="list-style-type: none">• Housing - High impact thermoplastic (UL 94 V-0)• IDC Contact - Phosphor bronze with 100 micro-inch tin over nickel under plating• Nose Contact - Beryllium copper with precious metal plating with nickel under-plating
Style	RJ-45 Jack
Temperature Rating	Max Continuous- 75° C, Minimum- -40° C Without



UPC
Impact
883778500022

Dimensions

Display Size
Standard Sized Product

Electrical Ratings

Connectivity	RJ45 Jack to IDC Punch Down
Contact Resistance	Per TIA
Insertion Loss	Per TIA
Withstand Voltage	1,000 Vac @ 60 Hz

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• 6-Position USOC Compliant• CSA Certified• Mechanical TIA-568• RoHS Compliant• UL Listed 1872
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	25
Number of Pieces in Package	1
Pallet Quantity	9600

Product Assets

[Catalog Page - PREM V10 Catalog Page](#)
[Catalog Page - PREM S10 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Specifications - NSJUW Specification Sheet English](#)
[Specifications - NSJUW Specification Sheet French](#)