

Net Select, Module, Combo,
Telephone/Video, 6-Port

By Hubbell Premise Wiring
Catalog # [NSOTVM6](#)



Net Select, Module, Combo, Telephone/Video, 6-Port

Features

- Meets FCC Part 68 standard
- All data and phone modules 568A wired
- Made of High impact plastic resistant material

Application

Combination

General

Catalog Number	NSOTVM6
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	6-Port Telephone/Video
Material - Mounting Hardware	Screw Mounting
Specifications	• Dimensions - 6.47 in. W x 2.95 in. H • Material - High impact plastic
Style	Combination
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Combination

UPC

883778503931

Dimensions

Display Size

Standard Sized Product

Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s)	• Meets FCC Part 68 Standard • RoHS Compliant • UL and cUL Listed
----------------------	---

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - PREM S7 CatalogPage](#)
[Catalog Page - PREM V7 CatalogPage](#)
[Catalog Page - PREM S07 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Specifications - NSOTVM6 Specification Sheet French](#)
[Specifications - NSOTVM6 Specification Sheet English](#)