

Net Select, Module, Video Amp,
Fixed 10dB

By Hubbell Premise Wiring
Catalog # [NSOVAMP](#)



Net Select, Module, Video Amp, Fixed 10dB

Application

Video

General

Catalog Number	NSOVAMP
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Fixed 10dB Video Amp, 125V
Material - Mounting Hardware	Screw Mounting
Specifications	• Dimensions - 6.47 in. W x 2.95 in. H • Material - High impact plastic
Style	Video
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Video
UPC	883778500336

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s)	• RoHS Compliant • UL and cUL Listed
----------------------	--

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - PREM V8 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - Residential Catalog](#)
- [Specifications - NSOVAMP Specification Sheet English](#)
- [Specifications - NSOVAMP Specification Sheet French](#)