

Cat6A Shielded Ethernet Cable, 5'
Patch Cord, 10GHz, Blue

By Hubbell Premise Wiring
Catalog # [PC6AB05](#)



5 ft. Blue Patch Cord, High-Performance Category 6A Shielded Ethernet Cable

Features

- Engineered for 10GbE Application Assurance
- Delivering Maximum Bandwidth Beyond 625MHz
- Experience Component Compliant ANEXT Performance
- Qualified to 150% of 802.3bt PoE Current Level

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	PC6AB05
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Shielded Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Specifications	• Conductor - 26AWG FTP • Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating • Jacket - Flame-Retardant PVC-CM Rated • Plug Body - Polycarbonate UL 94V-0 • Plug Boot - PVC
Temperature Rating	Per TIA
Type	Shielded

UPC 662620204000

Dimensions

Length	5 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	• ANSI/TIA/EIA-568-C.2 Category 6A Component • ISO 11801/60603-7-41 Category 6A Component
----------------------	---

Logistics

Carton Quantity	150
-----------------	-----

Product Assets

[Catalog Page - PREM D04 Catalog Page](#)
[Catalog Page - PREM D4 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Specifications - PC6AB05 Specification Sheet English](#)
[Specifications - PC6AB05 Specification Sheet French](#)