

Patch Cord, 10Gig, PC6A, Blue, 10' Length

By Hubbell Premise Wiring
Catalog # [PC6AB10](#)



Patch Cord, 10Gig, PC6A, Blue, 10' Length

Features

-
-
-
-

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	PC6AB10
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Shielded Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Specifications	- Conductor - 26AWG FTP - Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating - Jacket - Flame-Retardant PVC-CM Rated - Plug Body - Polycarbonate UL 94V-0 - Plug Boot - PVC
Temperature Rating	Per TIA
Type	Shielded

UPC662620204024

Dimensions

Length	10 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	- ANSI/TIA/EIA-568-C.2 Category 6A Component - ISO 11801/60603-7-41 Category 6A Component
----------------------	---

Logistics

Carton Quantity	90
-----------------	----

Product Assets

[Catalog Page - PREM D04 Catalog Page](#)
[Catalog Page - PREM D4 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Specifications - PC6AB10 Specification Sheet English](#)