

Category 6A MPTL Plug with 90°
Cable Exit

By Hubbell Premise Wiring
Catalog # [SP6A90](#)



NEXTSPEED® Category 6A MPTL Plug with 90° Cable Exit

Features

- Rugged die-cast housing supports shielded and non-shielded applications
- Category 6A channel compliant
- Cable Exit Direction Adjustable in 90° Increments
- Easily Re-Terminate
- Cord compression nut provides uniform pressure and superior strain relief

Performance

TIA Channel Compliant

General

Catalog Number	SP6A90
Contact Point Material	Copper Alloy with Gold Over Plating
Material - Housing	Zinc die-cast
Operating Cycles	750 Minimum
Series	Cat 6A
Size	0.62 (16) x 0.56 (14) x 2.0 (51)
UPC	662620666440

Dimensions

Dimensions	0.62 (16) x 0.56 (14) x 2.0 (51)
------------	----------------------------------

Electrical Ratings

Withstand Voltage	1,000 Vac @ 60 Hz
-------------------	-------------------

Certifications And Compliance

Industry Standard(s)	ANSI/TIA/EIA-568 Category 6A Channel,UL 1863 - Communications-Circuit Accessory,IEC60512-99-002 POE Disconnection Endurance,UL 2043 - Suitable for Air-Handling Spaces,RoHS Compliant
----------------------	---

Logistics

Carton Quantity	24
Number of Pieces in Package	1

Product Assets

- [Catalog Page - PREM B06 Catalog Page](#)
- [Catalog Page - PREM A04 Catalog Page](#)
- [Catalog Page - PREM B6 CatalogPage](#)
- [Catalog Page - PREM A05 Catalog Page](#)
- [Catalog Page - PREM A4 CatalogPage](#)
- [Catalog Page - PREM A5 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - netSELECT Category 6A End to End UTP System](#)
- [Literature - Catch the Wi-Fi 6 Wave](#)
- [Literature - Premise MPTL Assembly with Cobra-Lock Termination](#)
- [Specifications - SP6A90 Specification Sheet French](#)
- [Specifications - SP6A90 Specification Sheet English](#)