

HUBBELL

Premise Wiring

PROClick Connector, SC, OM3/OM4, Aqua, 12 Pack

By Hubbell Premise Wiring
Catalog # [FCSC900K50GM12](#)

Fiber Optic Connectors, ProClick SC, OM3/OM4, Pre-Polished, 10GHz 900, 12Pack.

Application

Interconnect

Performance

- Optical - Insertion loss - 0.5dB (0.35dB typical), 0.75dB max
- Optical - Mating durability - 500 cycles <
- 0.1dB change
- Optical - Multimode return loss - 35dB Typ, 22dB minimum
- Optical - Singlemode return loss - 55dB Typ, 40dB minimum
- Environmental - Operating temperature - 0 °C to +70 °C

General

Adapter Type	SC
Catalog Number	FCSC900K50GM12
Color	Aqua
Connector Type	SC
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	SC
Material	Ceramic
Material - Mounting Hardware	Fiber Termination, No Polish
Repeatability	0.1 dB
Service Life	500 matings
Specifications	<ul style="list-style-type: none">• Cable Type - 900/250 QM• Ferrule Material - Zirconia ceramic, UPC polish• Fiber Type - 50QM, OM3
Style	PROclick
Sub Brand	OptiChannel



Temperature Rating	0C to 70C
UPC	662620224077

Dimensions

Display Size	2.5 mm
--------------	--------

Electrical Ratings

Connectivity	Fiber Optic Connector
Insertion Loss	0.75 dB Max
Return Loss	26

Conductor Related

Fiber Size	125 Micron
Fiber Type	OM3/OM4, MM

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Telcordia GR-326-CORE• TIA-568-C.3• TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	10
Pallet Quantity	1610

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)
[Literature - FIBERHUBB PROclick® Fiber Connectors](#)
[Literature - PROclick® Fiber Connectors](#)
[Specifications - FCSC900K50GM12](#)