

HUBBELL Premise Wiring

FSP Adapter Panel, 6-Fiber, SC Simplex, 6-Port, Loaded with 6 Adapters, Phosphor Bronze, Blue

By Hubbell Premise Wiring
Catalog # [FSPSC6](#)



FSP Adapter Panel, 6-Fiber, SC Simplex, 6-Port, Loaded with 6
Adapters, Phosphor Bronze, Blue

Application

Interconnect

Performance

- Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Adapter Type	SC Simplex
Catalog Number	FSPSC6
Color	Blue
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) SC Simplex
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Specifications	<ul style="list-style-type: none">• Dimensions - 1.1" W X 5.1" H• Finish - Durable black powder coat• Material - 16ga cold rolled steel

- Sleeve Material - Phosphor Bronze
- Temperature Rating
UPC
-40C to +85C
662620827797

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity Receptacle
Insertion Loss 0.30 dB
Return Loss 26

Conductor Related

Fiber Size 125 Micron
Fiber Type Multimode

Certifications And Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 4

Product Assets

[Specifications - FSPSC6](#)