

HUBBELL Premise Wiring

HFCD14 Series Indoor/Outdoor Tight Buffer, 6 strand, I/O Tight Buffer Riser, OM3, MM, Black Jacket

By Hubbell Premise Wiring
Catalog # [HFCD14006R3BK](#)

HFCD14 Series Indoor/Outdoor Tight Buffer, 6 strand, I/O Tight Buffer Riser, OM3, MM , Black Jacket.



Application

Data Transmission

General

| | |
|--------------------|-------------------------------|
| Attenuation | 3.5/1.5 Db per Kilometer |
| Bandwidth | 2000 bps |
| Cable Rating | I/O Tight Buffer Riser |
| Catalog Number | HFCD14006R3BK |
| Color | Black |
| Material - Jacket | PVC |
| Sub Brand | Fiber Optics |
| Temperature Rating | -20 Degrees C to 70 Degrees C |
| Type | Cable |
| UPC | 662620333830 |

Electrical Ratings

Wavelength 850/1300 Nanometers

Conductor Related

| | |
|------------------|---------|
| Fiber Size | OM3 |
| Fiber Type | OM3, MM |
| Number of Fibers | 6 |

Certifications And Compliance

| | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none">ANSI/ICEA S-83-596NFPA-262/UL910/CSA FT-4Telcordia GR-409 and GR-20TIA-568.3-D |
|----------------------|---|

Product Assets

[Literature - Fiber Optic Cable Guide](#)
[Specifications - HFCD14006R3BK](#)