

HUBBELL Premise Wiring

HFCD19 Series Indoor/Outdoor Tight Buffer, 12 strand, Plenum, Armored, OM4, MM, Black Jacket

By Hubbell Premise Wiring
Catalog # [HFCD19012P4BK](#)



Application

Data Transmission

General

Attenuation	3.5/1.5 Db per Kilometer
Bandwidth	4000 bps
Cable Rating	Plenum, Armored
Catalog Number	HFCD19012P4BK
Color	Black
Material - Jacket Specifications	PVC <ul style="list-style-type: none">Armor - Aluminum InterlockCable Diameter in (mm) - 0.63 (16)Cable Weight (lb/kft) - 170Construction - Single Unit, Aramid Strength MemberFiber Coating - 900 Micron PVC Tight Buffer
Sub Brand	Fiber Optics
Temperature Rating	0 Degrees C to 70 Degrees C

Type
UPC

Cable
662620332321

Electrical Ratings

Wavelength 850/1300 Nanometers

Conductor Related

Fiber Size OM4
Fiber Type OM4, MM
Number of Fibers 12

Certifications And Compliance

Industry Standard(s)

- ANSI/ICEA S-83-596
- NFPA-262/UL910/CSA FT-6
- Telcordia GR-409
- TIA-568.3-D

Product Assets

[Literature - Fiber Optic Cable Guide](#)
[Specifications - HFCD19012P4BK](#)