

HUBBELL Premise Wiring

HFCD19024P4BK

By Hubbell Premise Wiring
Catalog # [HFCD19024P4BK](#)

HFCD19 Series Indoor/Outdoor Tight Buffer, 24 strand, Plenum, Armored, OM4, MM , Black Jacket.



General

Application	Data Transmission
Attenuation	3.5/1.5 Db per Kilometer
Bandwidth	4000 bps
Cable Rating	Plenum, Armored
Catalog Number	HFCD19024P4BK
Color	Black
Material - Jacket	PVC
Sub Brand	Fiber Optics
Temperature Rating	0 Degrees C to 70 Degrees C
Type	Cable
UPC	662620332352

Electrical Ratings

Wavelength	850/1300 Nanometers
------------	---------------------

Conductor Related

Fiber Size	OM4
Fiber Type	OM4, MM
Number of Fibers	24

Certifications And Compliance

Industry Standard(s)	ANSI/ICEA S-83-596
	NFPA-262/UL910/CSA FT-6
	Telcordia GR-409
	TIA-568.3-D

Product Assets

[Literature - Fiber Optic Cable Guide](#)