

HUBBELL Premise Wiring

Jack, Keystone, Cat 6A, Universal, Red

By Hubbell Premise Wiring
Catalog # [HJ6AR](#)

Jack, Keystone, Cat 6A, Universal, Red



General

Application	Telephone and Data Distribution Jack
Catalog Number	HJ6AR
Color	Red
Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	NEXTSPEED Ascent Category 6A Jacks
Material - Mounting Hardware	Keystone
Performance	Electrical - 1.5 dB min NEXT margin over ISO component - Electrical - 4.5db min NEXT margin over TIA 568-C.2 component at 500MHz - Electrical - Enhanced common mode design eliminates residual and reflected NEXT and ANEXT - Electrical - Qualified to 150% of 802.3bt PoE Current Level - General Information - 100% factory tested - General Information - Backward compatible to Category 6, & 5e - General Information - HJ6Axx Jacks are not compatible with RJ11, RJ14 or RJ25 6-position plugs - General Information - Icon Compatible Supporting 606-B requirements - Mechanical - Contact performance confirmed over the full range of ISO/FCC compliant plug - Mechanical - IDC Contact Termination: 10x - Mechanical - Keystone Latching Force: 25 lbs. - Mechanical - Nose Contact Mating Cycles: 2000 -
Series	Cat 6A
Temperature Rating	Per TIA
UPC	662620213996

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Insulation Displacement
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Certifications And Compliance

Industry Standard(s)	ANSI/TIA/EIA-568-C.2 Category 6A Component ISO 11801/60603-7-41 Category 6A Component
----------------------	--

Logistics

Carton Quantity	25
Number of Pieces in Package	Single

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
PREM_MX-HJ6AR-SPEC-EN | REV 6/2024