

HUBBELL Premise Wiring

USOC XCELERATOR™ Jack

By Hubbell Premise Wiring
Catalog # [HXJUBK](#)



XCELERATOR™ RJ25 USOC modular jacks support various telephony applications. The innovative angled QuickLace™ termination towers provide ample room for lacing, accelerating the termination.

Application

Telephone

Performance

USOC

General

Catalog Number	HXJUBK
Color	Black
Construction Material - Main Contact	Thermoplastic IDC: Phosphor Bronze with 100 Micro-Inch Tin Over Plating
Contact Point Material	Beryllium Copper with Gold Over Plating
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Modular Jack
Material - Housing	High-impact thermoplastic (UL 94V-0)
Material - Mounting Hardware	Keystone
Mounting Type	Snap-fit
Operating Cycles	2000 Plug
Series	USOC
Size	0.86 (22) x 0.67 (17) x 1.29 (33)
Specifications	<ul style="list-style-type: none">Housing - High impact thermoplastic (UL 94 V-0)IDC Contact - Phosphor bronze with 100 micro-inch tin over nickel under platingNose Contact - Beryllium copper with precious metal

plating with nickel under-plating

Style
Temperature Rating

RJ-45 Jack
Max Continuous- 75° C,
Minimum- -40° C Without Impact

Type
UPC

Modular Jack
662620824697

Dimensions

Display Size

Standard Sized Product

Electrical Ratings

Connectivity
Contact Resistance
Withstand Voltage

RJ45 Jack to IDC Punch Down
100 Ohm
1,000 Vac @ 60 Hz

Certifications And Compliance

Industry Standard(s)

- 6-Position USOC Compliant
- CSA Certified
- Mechanical TIA-568
- RoHS Compliant
- UL Listed 1864

Logistics

Carton Quantity 25
Number of Pieces in Package 1

Product Assets

[Literature - HDPJ High Density Jack Panels Specifications - HXJUBK](#)