


HUBBELL Premise Wiring

USOC XCELERATOR™ Jack

By Hubbell Premise Wiring
Catalog # [HXJUR](#)

Telephone/Data, Jack, XCELERATOR, USOC 6-Position



Application

- Telephone

Performance

USOC

General

Catalog Number	HXJUR
Color	Red
Construction Material - Main Contact	Thermoplastic IDC: Phosphor Bronze with 100 Micro-Inch Tin Over Plating
Contact Point Material	Beryllium Copper with Gold Over Plating
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Modular Jack
Material - Housing	High-impact thermoplastic (UL 94V-0)
Material - Mounting Hardware	Keystone
Mounting Type	Snap-fit
Operating Cycles	2000 Plug
Series	USOC
Size	0.86 (22) x 0.67 (17) x 1.29 (33)
Specifications	<ul style="list-style-type: none">• Housing - High impact thermoplastic (UL 94 V-0)• IDC Contact - Phosphor bronze with 100 micro-inch tin over nickel under plating• Nose Contact - Beryllium copper with precious metal

plating with nickel under-plating

Style	RJ-45 Jack
Temperature Rating	Max Continuous- 75° C, Minimum- -40° C Without Impact
Type	Modular Jack
UPC	662620824819

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	RJ45 Jack to IDC Punch Down
Contact Resistance	100 Ohm
Withstand Voltage	1,000 Vac @ 60 Hz

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• 6-Position USOC Compliant• CSA Certified• Mechanical TIA-568• RoHS Compliant• UL Listed 1864
----------------------	--

Logistics

Carton Quantity	25
Number of Pieces in Package	1

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Literature - HDPJ High Density Jack Panels](#)
[Specifications - HXJUR](#)