

# HUBBELL

## Premise Wiring

### Cabinet Components, Power Strip, 19" Rack Mount, 4 Front Outlets, 4 Rear Outlets, NEMA 5-15R Plug, 15A/120V, Recessed



By Hubbell Premise Wiring  
Catalog # [MCCPSS19TS](#)

Cabinet Components, Power Strip, 19" Rack Mount, 4 Front Outlets, 4 Rear Outlets, NEMA 5-15R Plug, 15A/120V, Recessed

#### Features

- 19" Rack Mount
- 4 Front Outlets
- 4 Rear Outlets
- NEMA 5-15R Plug
- 15A/120V

#### Application

15A-120V

#### General

Catalog Number	MCCPSS19TS
Color	Black
Construction Material - Main	Steel
EU RoHS Indicator	Yes
Item Type	15A 125V
Receptacle Type	NEMA 5-15R
Sensing Range	19 IN
Sub Brand	Power Distribution
Type	Rack Mount
UPC	662620802770

#### Dimensions

Depth	5.25
Thickness	0.0781

#### Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	120 V
Voltage Rating Description	120 V

#### Certifications And Compliance

Industry Standard(s)	UL
----------------------	----

#### Logistics

Carton Quantity	1
-----------------	---

#### Product Assets

[Specifications - MCCPSS19TS](#)