

HUBBELL Premise Wiring

Fiber Cassette, Plug and Play Cassette, LC-MT, Multi Mode 50/125, 10GbE

By Hubbell Premise Wiring
Catalog # [OCLC50G](#)



Application

Interconnect

Performance

Optical - Total insertion loss - Less than 1.5dB (test data included)

General

Catalog Number	OCLC50G
Color	Aqua
EU RoHS Indicator	Yes
Environmental Conditions	Indoor
Item Type	LC Duplex to MTP
Material	Ceramic
Material - Mounting Hardware	Snap-In
Repeatability	0.1 dB
Service Life	500 matings
Specifications	<ul style="list-style-type: none">• Cassette Type - LC Duplex 12F• Dimensions - 5.1" H x 1.1" W x 2.75" D• Fiber Type - 50QM, OM3• Housing material - 16ga powder coated steel• MTP connector - 12-fiber male receptacle on back side• Sleeve material - Ceramic

Style	LC Duplex 12F
Temperature Rating	0C to 70C
UPC	662620200538

Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

Electrical Ratings

Connectivity	Cassette
Insertion Loss	0.75 dB Max
Return Loss	55

Conductor Related

Fiber Size	250 Micron
Fiber Type	OM3

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Telcordia GR-326-CORE• TIA-568-C.3• TIA-604-FOCIS
----------------------	-----------------------------------------------------------------------------------------------------------------------

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)
[Specifications - PREMISE_OCLC50G_spec](#)