

# HUBBELL Premise Wiring

## Fiber High Density Cassette, , LC Duplex to MTP, Aqua

By Hubbell Premise Wiring  
Catalog # [OCLCHD50G4](#)



### Features

- OM2 Fiber
- 12-Fiber Strands
- OM4 Fiber.

### Application

Interconnect

### General

|                              |                  |
|------------------------------|------------------|
| Catalog Number               | OCLCHD50G4       |
| EU RoHS Indicator            | Yes              |
| Environmental Conditions     | Indoor           |
| Item Type                    | LC Duplex to MTP |
| Material - Mounting Hardware | Snap-In          |
| Repeatability                | 0.1 dB           |
| Service Life                 | 500 matings      |
| Style                        | Ultra Compact    |
| Temperature Rating           | 0C to 70C        |
| UPC                          | 662620228471     |

### Dimensions

Display Size 5.1" X 1.1"

### Electrical Ratings

|                |             |
|----------------|-------------|
| Connectivity   | Receptacle  |
| Insertion Loss | 0.75 dB Max |
| Return Loss    | 55          |

### Conductor Related

Fiber Size 125 Micron

### Logistics

Carton Quantity 25

### Product Assets

[Brochures - Fiber Connectivity Product Guide](#)  
[Sell Sheets - FIBERHUBB Ultra Compact Fiber LC to MPO Cassette Modules](#)  
[Sell Sheets - FIBERHUBB High Density 144 Port 1U Fiber Enclosure](#)  
[Specifications - OCLCHD50G4](#)