

HUBBELL Premise Wiring

Fiber LGX Cassette, OM3, LC Duplex to MTP, Aqua

By Hubbell Premise Wiring

Catalog # [OCLCQ50G](#)



Application

Interconnect

Performance

Optical - Total insertion loss - Less than 1.5dB (test data included)

General

Catalog Number	OCLCQ50G
Color	Aqua
EU RoHS Indicator	Yes
Environmental Conditions	Indoor
Item Type	LC Quad to MTP
Material	Ceramic
Material - Mounting Hardware	Snap-In
Repeatability	0.1 dB
Service Life	500 matings
Specifications	<ul style="list-style-type: none">Cassette Type - LC Quad 24FDimensions - 5.1" H x 1.1" W x 2.75" DFiber Type - 50QM, OM3Housing material - 16ga powder coated steelMTP connector - 12-fiber male receptacle on back sideSleeve material - Ceramic

Style	LC Quad 24F
Temperature Rating	0C to 70C
UPC	662620214467

Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

Electrical Ratings

Connectivity	Cassette
Insertion Loss	0.75 dB Max
Return Loss	55

Conductor Related

Fiber Size	250 Micron
Fiber Type	OM3

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">Telcordia GR-326-CORETIA-568-C.3TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	35
-----------------	----

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)
[Specifications - PREMISE_OCLCQ50G_spec](#)