

HUBBELL Premise Wiring

Patch Cord, 10Gig, PC6A, Gray, 7' Length

By Hubbell Premise Wiring
Catalog # [PC6AGY07](#)



Patch Cord, 10Gig, PC6A, Gray, 7' Length

Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	PC6AGY07
Color	Gray
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Shielded Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Specifications	<ul style="list-style-type: none">• Conductor - 26AWG FTP• Contact Plating - 50 micro-inch Gold with 100 micro-inch under plating• Jacket - Flame-Retardant PVC-CM Rated• Plug Body - Polycarbonate UL 94V-0• Plug Boot - PVC
Temperature Rating	Per TIA
Type	Shielded
UPC	662620204086

Dimensions

Length	7 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• ANSI/TIA/EIA-568-C.2 Category 6A Component• ISO 11801/60603-7-41 Category 6A Component
----------------------	---

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

[Specifications - PC6AGY07](#)