

# HUBBELL Premise Wiring

## Copper Solutions, Patch Cords, Cat6, Shielded, Gray, 10' Length

By Hubbell Premise Wiring  
Catalog # [PS6GY10](#)



Copper Solutions, Patch Cords, Cat6,Shielded, Gray, 10' Length

### Features

- Cat6
- Shielded
- Gray
- 10' Length

### Application

Data Transmission

### General

Attenuation	.1dB
Boot Type	Strain Relief
Catalog Number	PS6GY10
Color	Gray
Plug Type	RJ45
Sub Brand	Copper Patch Cords
Temperature Rating	Per TIA
Type	Cat6, PS6
UPC	662620604688

### Dimensions

Length	10 ft
Outside Diameter	0.218 in

### Electrical Ratings

Voltage Rating	300 VAC
----------------	---------

### Conductor Related

Conductor Stranding	Solid
Number of Conductors	8-Conductor
Wire Size	#24 AWG

### Certifications And Compliance

Industry Standard(s)	UL1863
----------------------	--------

### Product Assets

[Specifications - PS6GY10](#)