



# Tork Photocontrol Remote Photo Cell

By Progress Lighting  
Catalog # PTORK3010



## Features

- 
- 
- 

## General

Can be mounted up or down	No
Catalog Number	PTORK3010
Category General	Outdoor
Color	Gray
Color Generic	Grey
Construction Material - Main	Lexan(R)
Convertible fixture includes both mounts	No
Dusk to Dawn	No
EU RoHS Indicator	Contact Manufacturer
Finish Name	Unfinished
Finish Type	Unfinished
Fixture Type	Outdoor Accessory
Indoor/Outdoor	Outdoor
Lamp Included	No
Lifestyle	Traditional
Mount location	Wall
Mounting for outlet box included	strap
New Products	No
Photocell	Yes
Power Source	Hardwired
Power Source Required?	Yes
Prewired	Yes
Room Type	Outdoor
Service Life	On Website=Yes
Style	Utilitarian/Commodity
UPC	786261600219
Warranty Length	1-year Limited Warranty

## Dimensions

Dimensions	3 in x 3 in x 5.625 in
Height	5.625 in
Length	3 in

Note Weight of fixture exceeds NEC limits	No
Weight	0.21 lb
Width	3 in
Width Diameter Descriptor	W.

## Electrical Ratings

Voltage Rating	120 V
----------------	-------

## Certifications And Compliance

Americans with Disabilities Act	No
Buy American Compliant	Yes
Certified Listed	cULus
Certified Listed Location	Dry Location Listed
DarkSky	No
ENERGY STAR Certified	No
Energy Efficient	Yes
EnergyStar	No
JA8	No
Other Heavy Metal Content	No
Indicator	
Title 20	N/A
Title 22	No
Title 24	Yes

## Logistics

Carton Quantity	96
Pallet Quantity	1920

## Resources

Instruction Sheet Number	PTORK3010
--------------------------	-----------

## Product Assets

- [Catalog Page - PROG\\_CAT133\\_1097\\_pages](#)
- [Certifications - California Proposition 65 WARNING](#)
- [Installation Manuals - PROG\\_PTORK3010\\_install](#)
- [Product Cross Section Image\(s\) - PROG\\_PTORK3010dimensions\\_silo](#)
- [Warranty - PROGRESS LIGHTING LIMITED WARRANTY](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
PROG-PTORK3010-SPEC-EN | REV 1/2025