

## Project:

Fixture Type:

Location:

Contact:

Damp location listed PROGRESS LED

# Lamp

### **Description:**

Maxlite's G9 retrofit lamp is an energy-efficient alternative to Halogen T4 G9 based lamps. The 3 watt lamp captures the traditional form factor of this light source while offering a powerful light distribution similar to halogen lamps. 270 lumens, 90 lumens/watt (delivered). 25,000 hour life (L70 standards).Light Appearance of 2700K (soft white).

#### **Specifications:**

- G9 base LED bulb
- 270 lumens, 90 lumens/watt (delivered).
- 25,000 hour life (L70 standards).
- Light Appearance: 2700K (soft white).
- Dimmable down to 10%.
- Suitable for use in damp locations.
- 3 year limited warranty.
- Dimmable to 10% brightness (See Dimming Notes)
- •

#### Performance:

Input Power	3w
Input Voltage	120 V
Lumens/LPW (Delivered)	270/90 (LM-79)
CCT	2700 К
Min. Start Temp	-4 °F
Warranty	3 year warranty
Labels	cULus Damp location listed

## 3G9DLED27

#### Images:



#### **Dimensions:**

Width: 0.66" Height: 1.88"



# Lamp

# Damp location listed PROGRESS LED

# 3G9DLED27

### **Dimming Notes:**

3G9DLED27 is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

## **Dimming Controls**

utron CTCL-153P	
utron DVCL-153P	
utron LGCL-153P	
utron S-600	
eviton IPL06	
eviton IPI10	
eviton 6683-IW	

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.