

Project: \_\_\_\_\_  
 Fixture Type: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Contact: \_\_\_\_\_

## DFS SERIES

### LED Decorative Double Layer Round Drum

### Specifications:

#### Description:

Family offering of ceiling, cable pendant, and wall mount decorative fabric/acrylic diffusers. The DFS Series combines modern aesthetics and quality performance by offering a wide array of choices for size, shape and material finish. With the possibility for custom sizes and finishes, this offering is sure to meet every design need. Ideal for hospitality, multi-family, commercial, and residential applications.

#### Features:

- Family offering of surface mount, cable pendant mount and accompanying sconces.
- Fabricated round double layer shade uniquely crafted with a outer laminated fabric material.
- Shade sizes of 16", 18" and 23". Five fabric and acrylic finish options available.
- Integrated with high performance LED light engine rated at 50,000 hours, 3000K, 90 CRI
- Cable pendant mount option with white and nickel finish choices.

#### Specifications:

- **Construction:** Light weight, full acrylic decorative shade with outer layer of decorative fabric. Option of double laminated fabric material allows for a durable and cleanable surface finish. Shades attach to a metal pan chassis that includes a high performance LED integrated module. LED integrated module includes spread optics to provide clean and even distribution on all surface areas of decorative shade.
- **Installation/Mounting:** Surface housing option to be installed ceiling mount to standard 4" recessed outlet box. Cable pendant housing option supplied with canopy mount and 10ft of cable/cord. Canopy to be installed ceiling mount to standard 4" recessed outlet box. Mounting screws for outlet box included. Shade attaches to chassis via 3 mounting pins, included.
- **Electrical:** 120V/60 Hz., dimmable to 10%
- **Listing:** cULus label for Damp Locations. 5 Year limited warranty.

#### Finish Options:



#### Canopy Finish Options:



#### Images:



#### Dimensions:

	A	B	C	D
16	4.5"	5.4"	16"	13.4"
18	4.5"	5.4"	18"	15"
23	4.5"	5.4"	23.25"	19.25"

#### Performance:

	16" Surface Mount with WTL finish	18" Surface Mount with FAW finish
Lumens	1165	1723
Watts	17.2	25.6
Amps	0.146 / 0.064	0.224 / 0.097

#### Catalog Number:

Series	- Mounting	- Shape	- Size	- Shade Finish	- Wattage	- Voltage	- CRI/ CCT	- Canopy Finish
<b>PCDFS</b> - Decorative Fabric Shade	<b>SM</b> - Surface Mount  <b>CM</b> - Cable Pendant Mount	<b>DL</b> - Double Layer	<b>16</b> - 16" <b>18</b> - 18" <b>23</b> - 23"	<b>WTL</b> - White Linen <b>BGL</b> - Beige Linen <b>BKL</b> - Black Linen <b>GYL</b> - Gray Linen <b>LWT</b> - Double Laminated White Linen <b>LBG</b> - Double Laminated Beige Linen <b>FAW</b> - Full Acrylic White	<b>17</b> - 17W <sup>1</sup> <b>25</b> - 25W <sup>2</sup> <b>32</b> - 32W <sup>3</sup>	<b>120V</b> - 120V/60Hz	<b>930</b> - 90CRI/ 3000K	Blank (surface mount) <b>WT</b> - White <sup>4</sup> <b>BN</b> - Brush <sup>4</sup> Nickel

<sup>1</sup> - Wattage specific to 16" size only

<sup>2</sup> - Wattage specific to 18" size only

<sup>3</sup> - Wattage specific to 23" size only

<sup>4</sup> - CM mounting only