

DFW SERIES

LED Decorative Vertical Sweep Sconce

Specifications:

Description:

Family offering of ceiling, cable pendant, and wall mount decorative fabric/acrylic diffusers. The DFS Series combines modern aesthetics and quality performance by offering a wide array of choices for size, shape and material finish. With the possibility for custom sizes and finishes, this offering is sure to meet every design need. Ideal for hospitality, multi-family, commercial, and residential applications.

Features:

- Family offering of surface mount, cable pendant mount and accompanying sconces.
- Fabricated vertical sweep sconce uniquely crafted with a outer laminated fabric material.
- Four fabric finish options available.
- Integrated with high performance LED light engine rated at 50,000 hours, 3000K, 90 CRI

Specifications:

- **Construction:** Light weight, full acrylic decorative sconce with outer layer of decorative fabric. Option of double laminated fabric material allows for a durable and cleanable surface finish. Sconces attach to a metal pan chassis that includes a high performance LED integrated module. LED integrated module includes spread optics to provide clean and even distribution on all surface areas of decorative sconce.
- **Installation/Mounting:** Wall mounted; to be installed with standard 4" recessed outlet box. Mounting screws for outlet box included. Sconce shade attaches to metal chassis via 2 mounting clips, included.
- **Electrical:** 120V/60 Hz., dimmable to 10%
- **Listing:** cULus label for Damp Locations. 5 Year limited warranty.

Fabric Finish Options:



Catalog Number:

Series	- Mounting	- Shape	- Material Finish	- Wattage	- Voltage	- CRI/CCT
PCDFW - Decorative Fabric Wall Sconce	WM - Wall Mount	VS - Vertical Sweep	WTL - White Linen BGL - Beige Linen BKL - Black Linen GYL - Gray Linen LWT - Double Laminated White Linen LBG - Double Laminated Beige Linen	17W - 17W	120V - 120V/60Hz	930 - 90CRI/3000K

Images:



PCDFW-WM-VS-WTL



PCDFW-WM-VS-GYL

Dimensions:

