

Project:

Fixture Type:

Location:

T8 LED Lamp

Lamp socket Mounted • Damp Location Listed PROGRESS LED

Contact:

Description:

Accessory bulb to give you options and design versatility when creating your desired lighting experience. Elongated bulb with clear glass and a candelabra base. Dimmable to 10%. Features 4w with 2700k color temperature.

Specifications:

- · Clear glass
- · Filament bulb.
- · Candelabra base
- 4w
- 2700K
- · Measures 15/16-inch width by 3-7/8-inch height.
- 3-year limited warranty.
- · Fully dimmable.

Performance:

Number of Modules	1
Input Power	4 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	300/75 (LM-79)
CCT	2700 K
CRI	90 CRI
Life (hours)	15000 (L70/TM-21)
Min. Start Temp	-30 °C
Warranty	3-year Limited Warranty
Labels	cULus Damp Location Listed
	Meets California Title 24 JA8-2016

EF4T8D927/JA8



Dimensions:

Diameter: 0-15/16 in Height: 3-15/16 in

