

9" LED Lamp

Lamp socket Mounted • Damp Location Listed **PROGRESS LED**

Description:

Accessory bulb to give you options and design versatility when creating your desired lighting experience. Elongated bulb with clear glass and a medium base. Dimmable to 10%. Features 6.5w with 2700K color temperature.

Specifications:

- Clear glass
- Filament bulb.
- 6.5w
- 2700K
- 15,000 hours
- Measures 1.3-inch width by 8-7/8-inch height.
- 3-year Limited Warranty
- Fully dimmable.

Performance:

Number of Modules	1
Input Power	6.5 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	600/92 (LM-79)
CCT	2700 K
CRI	90 CRI
Life (hours)	15000 (L70/TM-21)
Min. Start Temp	-30 °C
Warranty	3-year Limited Warranty
Labels	cETLus Damp Location Listed Meets California Title 24 JA8-2016

EF6.5T10DL9927/JA8



Dimensions:

Diameter: 1.3 in
Height: 8-15/16 in