

Project:			
Fixture Type:			
Location:			
Contact:			



P2129-09 Arden

Arden Collection Three-Light Bath & Vanity

Category: Bath & Vanity Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Etched Glass Shade

Width: 24-1/2 in Height: 7-1/2 in Depth: 8-1/4 in

H/CTR: 4-5/8 in (glass facing up)

Etched Glass Shade Width: 5-7/8 in Height: 5 in

	Height: 5 in				
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION		
Wall mounted	Prewired	(3) Medium Base (E26) sockets	UL-CUL Damp Location Listed		
Mounting strap for outlet box included	6 inches of wire supplied	Lamp Type A-19	1-year Limited Warranty		
Fixture can be installed with glass facing up or down	120 V	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket			
back plate covers a standard 4" recessed outlet box: 7.9375" W., 4.5" ht., 0.8125" depth		Fully dimmable with dimmable bulbs.			