

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P2130-09

Arden

Arden Collection Four-Light Bath & Vanity

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched Glass Shade

Width: 34 in
 Height: 7-1/2 in
 Depth: 8-1/4 in
 H/CTR: 4-5/8 in (glass facing up)

Etched Glass Shade
 Width: 5-7/8 in
 Height: 5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	(4) Medium Base (E26) sockets	UL-CUL Damp Location Listed
Mounting strap for outlet box included	6 inches of wire supplied	Lamp Type A-19	1-year Limited Warranty
Fixture can be installed with glass facing up or down	120 V	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
back plate covers a standard 4" recessed outlet box: 7.9375" W., 4.5" ht., 0.8125" depth		Fully dimmable with dimmable bulbs.	