

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



## P2130-20

### Arden

Arden Collection Four-Light Bath & Vanity

**Category:** Bath & Vanity  
**Finish:** Antique Bronze (Painted)  
**Construction:** Steel Construction  
**Glass/Shade:** Etched Glass Shade

Width: 34 in  
 Height: 7-1/2 in  
 Depth: 8-1/4 in  
 H/CTR: 4-5/8 in (glass facing up)

Etched Glass Shade  
 Width: 5-7/8 in  
 Height: 5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	(4) Medium Base (E26) sockets	UL-CUL Damp Location Listed
Mounting strap for outlet box included	6 inches of wire supplied	Lamp Type A-19	1-year Limited Warranty
Fixture can be installed with glass facing up or down	120 V	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
back plate covers a standard 4" recessed outlet box: 7.9375" W, 4.5" ht., 0.8125" depth		Fully dimmable with dimmable bulbs.	