

Two-Light Bath

 Wall mounted • Damp location listed **PROGRESS LED**


P2143-1530K9

Description:

Two-Light LED modern wall fixture in Polished Chrome with geometric frosted glass shades and a replaceable LED module. This modern fixture is perfect for the bathroom. 3000K color temperature and 90 plus CRI.

Specifications:

- Polished Chrome (-15) (plated)
- Steel Construction
- Etched glass shades
- LED Module is replaceable (part # 93054049)
- Provides evenly diffused illumination for vanity applications.
- Geometric frosted glass shades.
- Features a replaceable LED module.
- 623 lumens 69.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified

Performance:

Number of Modules	2
Input Power	9w per module
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	623/69.2 (LM-82) per module
Lumens/LPW (Delivered)	1164/73.2 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified

Images:



Dimensions:

Width: 15-1/2"
 Depth: 4"
 Height: 4-3/4"
 H/CTR: 2-3/8" (glass facing up)

Glass
 Width: 3-1/4"
 Length: 6"
 Height: 3-7/8"

P2143-1530K9

Dimming Notes:

P2143 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Nova T NTELV-300

Lutron Vienti VTELV-600

Lutron Ariadni AYCL-153P

Lutron Diva DVCL-153P

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.