

Project: \_\_\_\_\_  
 Fixture Type: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Contact: \_\_\_\_\_

## P2194-15 Metric

Metric Collection Two-Light Bath & Vanity

**Category:** Bath & Vanity  
**Finish:** Polished Chrome (Plated)  
**Construction:** Steel Construction  
**Glass/Shade:** Etched/Painted White Inside Glass Shade



Width: 13 in  
 Height: 6-1/2 in  
 Depth: 5-1/4 in  
 H/CTR: 4-1/8 in (glass facing up)

Etched/Painted White Inside Glass Shade

| MOUNTING   | ELECTRICAL                | LAMPING  | ADDITIONAL INFORMATION      |
|--|---------------------------|--|-----------------------------|
| Wall mounted   | Prewired                  | (2) Medium Base (E26) sockets  | UL-CUL Damp Location Listed |
| Mounting strap for outlet box included   | 6 inches of wire supplied | Lamp Type A-19   | 1-year Limited Warranty     |
| Fixture can be installed with glass facing up or down                                  | 120 V                     | Incandescent: 100-watt MAX per socket<br>LED: 17.5-watt MAX per socket |                             |
| back plate covers a standard 4" recessed outlet box: 7.6875" W., 4.5625" ht., 1" depth |                           | Fully dimmable with dimmable bulbs.                                    |                             |