

roject.		
ixture Type:		
ocation:		

Springer

Ceiling Mounted • Dry Location Listed PROGRESS LED



Description:

Springer is a statement-making ceiling fan with a rustic flair and a rich Architectural Bronze finish and Distressed Walnut blades. The 12-blade, 60 in ceiling fan was inspired by the form and function of a windmill and is ideal for Farmhouse, Industrial and Transitional interior settings. A full function remote control with batteries is included along with a dual mount canopy that accommodates flat or sloped ceilings.

Specifications:

- 12-blade, 60" statement-making ceiling fan was inspired by the form and function of a windmill
- · Powerful and quiet DC Motor
- · Features Distressed Walnut finished blades
- · Springer ceiling fan with a rich Architectural Bronze finish and Distressed Walnut blades
- Beautiful and expansive in design, the indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- $\boldsymbol{\cdot}$ A full function six-speed remote with batteries and reverse direction control is included
- Springer ceiling fan adds form and function by providing increased air circulation in rooms
- Oversized, texture die cast hanger ball reduces noise and wobble vibrations
- · Ideal for Farmhouse, Industrial and Transitional interior settings
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet
- Dual mount canopy that accommodates flat or sloped ceilings (sloped -22 degrees)
- Airflow: 6377 CFM Energy consumption: 32 watts (excluding lights) Airflow efficiency: 201 cfm/watt Fan on a downrod
- A 1" x 8" downrod is included. Longer accessory downrods can be ordered separately
- · This fan is not light kit adaptable.
- · ETL dry location listed
- · Limited Lifetime Warranty
- $\boldsymbol{\cdot}$ Canopy covers a standard 4" recessed outlet box
- Mounting bracket for outlet box included
- · 80 in of wire supplied

Performance:

Input Voltage	120 V
Input Frequency	60 Hz
Warranty	Limited Lifetime warranty
Labels	cETLus Dry Location Listed
	DC motor

P250000-129



Contact:



Dimensions:

Diameter: 60 in Height: 17-3/8 in

