

## Project:

Fixture Type:

Location:

Contact:

# Springer

### Ceiling downrod Mounted • Dry Location Listed

#### **Description:**

Springer Collection 60-Inch 12-Blade Matte Black DC Motor Farmhouse Windmill Ceiling Fan

#### **Specifications:**

- Canopy covers a standard 4" recessed outlet box: 6 in W., 2.25 in ht., 6 in depth
- Mounting Bracket
- + 80 in of wire supplied

#### **Performance:**

Input Voltage	120 V
Input Frequency	60 Hz
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime warranty
Labels	cETLus Dry Location Listed
	DC motor





P250000-31M

#### **Dimensions:**

Length: 60 in Diameter: 60 in Height: 17-3/8 in

EMERGYGUIDE	
Estimated Yearly Energy Cost \$6 3 1 1 34 Cost Range of Similar Models (19" – 84') • Based on 12 cents per KWh and 64 hours use per day • Your cost depends on rates and use	Airflow 4,396 Cubic Feet Per Minute - The higher the airflow, the more air the fan will move - Airflow Efficiency: 206 Cubic Feet Per Minute Per Watt
Energy Use: 21 Watts All estimates based on typical use, excluding lights	ftc.gov/energy