

Project:			
Fixture Type:			
Location:			
Contact:			

## **FARRIS**

## Ceiling mounted • Dry location listed

### **Description:**

Farris features three solid wood carved blades to form a sleek, modern design. The 60" ceiling fan includes an integrated LED light kit that is removable to provide the option in non-illuminated applications. Available in Brushed Nickel, Oil Rubbed Bronze and Graphite finishes. A full function remote control with batteries is included, and the dual mount canopy accommodates flat or sloped ceilings.

## **Specifications:**

- · Brushed Nickel (-009) (plated)
- · Steel construction
- Three-blade, 60" fan includes an integrated LED light kit that is removable to provide the option in nonilluminated applications
- · Powerful and quiet DC Motor
- · Features Gray Weathered Wood finished blades
- · Farris ceiling fan with Brushed Nickel finish and Gray Weathered Wood finished blades
- Light kit blank cover plate included if light is not desired
- Beautiful and expansive in design, the indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- The light kit contains a white opal glass shade and is comprised of a 18W dimmable 3000K LED module, offering 1400 lumens, 90+ CRI
- A full function six-speed remote with batteries and reverse direction control is included and controls full range dimming and fan speed capabilities
- · Farris ceiling fan adds form and function by providing increased air circulation in rooms
- · Oversized, texture die cast hanger ball reduces noise and wobble vibrations
- · Ideal for Modern, Contemporary and Industrial settings
- · As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet
- Dual mount canopy that accommodates flat or sloped ceilings (sloped -13 degrees)
- · A 1" x 6" downrod is included. Longer accessory downrods can be ordered separately
- · Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- · Mounting Yes for outlet box included
- · 80" of wire supplied
- Grey Weathered Wood blades, wood construction
- 18 blade pitch
- · Full function remote included
- · 6 Speed, Remote Reverse
- · Airflow: 7047 CFM\*
- Energy consumtion: 31 watts (excluding lights)\*
- Airflow efficiency: 224 cfm/watt\*
- \* Fan on a downrod

#### Performance:

Number of Modules	1	
Input Power	18w	
Input Voltage	120 V	
Input Frequency	60 Hz	
Lumens/LPW	1400/77 (LM-79)	
ССТ	3000 K	
CRI	90 CRI	
Life (hours)	50,000 (L70/TM-21)	
Warranty	Limited Lifetime	
Labels	cULus Dry location listed	

P250002-009-30

#### **Images:**



#### **Dimensions:**

Diameter: 60" Height: 15-1/2"



# **FARRIS**

Ceiling mounted • Dry location listed PROGRESS LED

P250002-009-30

## **Dimming Notes:**

P250002 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## **Dimming Controls**

Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron-DVCL-253P

Lutron - Caseta Wireless

IDevices - IDEV009

Leviton - 6672

Leviton - 6674

Lutron - AYCL-153P

Lutron - TGCL-153-PH-WH

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton -AWSMT-EAW

Lutron - N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.