

Project:

Fixture Type: Location:

Contact:

Ceiling mounted • Dry location listed PROGRESS LED

# FARRIS 60"

**Description:** 

Farris features three solid wood carved blades to form a sleek, modern design. The 60" ceiling fan includes an integrated LED light kit that is removable to provide the option in non-illuminated applications. Available in Brushed Nickel, Oil Rubbed Bronze and Graphite finishes. A full function remote control with batteries is included, and the dual mount canopy accommodates flat or sloped ceilings.

### **Specifications:**

- · Graphite (-143) (painted)
- Steel construction
- White opal glass diffuser
- Three-blade, 60" fan includes an integrated LED light kit that is removable to provide the option in nonilluminated applications
- · Powerful and quiet DC Motor
- Features Driftwood finished blades
- · Farris ceiling fan with Graphite finish and Driftwood finished blades
- Light kit blank cover plate included if light is not desired
- Beautiful and expansive in design, the indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- The light kit contains a white opal glass shade and is comprised of a 18W dimmable 3000K LED module, offering 1400 lumens, 90+ CRI
- A full function six-speed remote with batteries and reverse direction control is included and controls full range dimming and fan speed capabilities
- Farris ceiling fan adds form and function by providing increased air circulation in rooms
- · Oversized, texture die cast hanger ball reduces noise and wobble vibrations
- Ideal for Modern, Contemporary and Industrial settings
- · As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet
- Dual mount canopy that accommodates flat or sloped ceilings (sloped -13 degrees)
- A 1" x 6" downrod is included. Longer accessory downrods can be ordered separately
- UL dry location listed
- Limited Lifetime Warranty
- Dimmable to 10% brightness (See Dimming Notes)
- 80" of wire supplied
- Driftwood blades, wood construction
- 18 blade pitch
- Full function remote included
- 6 Speed, Remote Reverse
- Airflow: 7047 CFM\*
- Energy consumtion: 31 watts (excluding lights)\*
- Airflow efficiency: 224 cfm/watt\*
- \* Fan on a downrod

#### **Performance:**

Number of Modules	1
Input Power	18w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	1400/77 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
Warranty	Limited Lifetime
Labels	cULus Dry location listed

## P250002-143-30

#### Images:



**Dimensions:** 

Diameter: 60" Height: 15-1/2"



# FARRIS 60"

Ceiling mounted • Dry location listed PROGRESS LED

# P250002-143-30

### **Dimming Notes:**

P250002 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## **Dimming Controls**

Lutron - NTEVL-300
Lutron - DVELV-300P
Lutron-DVCL-253P
Lutron - Caseta Wireless
IDevices - IDEV009
Leviton – 6672
Leviton – 6674
Lutron - AYCL-153P
Lutron - TGCL-153-PH-WH
Lutron - AYLV-600P
Lutron - MAELV-601
Leviton -AWSMT-EAW
Lutron - N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.