

Project:
Fixture Type:
Location:

Kaysville

Ceiling Mounted • Damp Location Listed PROGRESS LED

Contact:

Description:

Kaysville Collection 6-Blade Grey Weathered Wood 56-Inch DC Motor LED Urban Industrial Ceiling Fan

Specifications:

- · White Opal Glass Bowl
- · Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 6.5 in W., 2.5 in ht., 6.5 in depth
- 80 in of wire supplied

Performance:

Number of Modules	1
Input Power	24 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,100
ССТ	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	cULus Damp Location Listed
	Meets California Title 24 JA8-2016
	DC motor





Dimensions:

Length: 56 in Diameter: 56 in Height: 17-1/4 in

White Opal Glass Bowl Width: 8-1/2 in Height: 3-1/8 in



Kaysville

Ceiling Mounted • Damp Location Listed PROGRESS LED

Dimming Notes:

P250003-143-30

P250003-143-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

IDevices IDEV009

Lutron NTEVL-300

Lutron DVELV-300P

Lutron TGCL-153-PH-WH

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.