

Project:

Fixture Type: Location:

Contact:

# TEASLEY

Ceiling mounted • Dry location listed

## **Description:**

## P250004-129

#### Images:

Featuring coastal influences and farmhouse charm, the Teasley 56" five-blade ceiling fan is suitable for a variety of interior settings. Clear seeded bell-shaped glass shades highlights the Architectural Bronze finish. Three LED lamps are included, offering energy efficiency and cost savings benefits for the home, while a dual mount canopy accommodates flat or sloped ceilings.

### **Specifications:**

- Architectural Bronze (-129) (painted)
- Steel construction
- Clear seeded Glass Bell
- The Teasley 56" 5-blade ceiling fan is suitable for a variety of interior settings
- Reversible Distressed Walnut and American Walnut blades
- Rich Architectural Bronze finish with Brushed Bronze accents
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- Clear seeded bell-shaped glass shades including three 2700K dimmable vintage LED lamps, offering 2400 lumens
- Features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light
- Pull chain is Brass
- · Add an accessory wall or remote control for added convenience
- Ideal for Traditional, Transitional and Farmhouse settings
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet
- Dual mount canopy that accommodates flat or sloped ceilings
- A 1" x 6" downrod is included. Longer accessory downrods can be ordered separately
- Teasley offers energy efficiency and cost savings benefits for the home
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting Yes for outlet box included
- 80" of wire supplied
- Distressed Walnut/American Walnut reversible blades, plywood construction
- Brass pull chain with Walnut fob
- 12.5 blade pitch
- Triple capacitor speed control, manual reverse control Speed, Manual Reverse
- Airflow: 5749 CFM\*
- Energy consumtion: 75 watts (excluding lights)\*
- Airflow efficiency: 76 cfm/watt\*
- \* Fan on a downrod

#### **Performance:**

Number of Modules	3
Input Power	7w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	2400/114 (LM-79) per module
CCT	2700 К
CRI	80 CRI
Life (hours)	15,000 (L70/TM-21)
Warranty	Limited Lifetime
Labels	ULus Dry location listed



#### **Dimensions:**

Diameter: 56" Height: 22-1/2"

Glass Width: 4-3/4" Height: 5-5/8"



# TEASLEY

Ceiling mounted • Dry location listed PROGRESS LED

# P250004-129

#### **Dimming Notes:**

P250004 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

### **Dimming Controls**

Lutron DV-603P
Lutron LGCL-153CL
Lutron CT-103P-WH
Leviton 6684
Almond LUXDM600-12
Leviton 6631-LA
Leviton IPI06
Leviton S-600P-WH
Lutron DV-603PR
Lutron S-600PR-WH

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.