

TEASLEY

Ceiling mounted • Dry location listed

Description:

Featuring coastal influences and farmhouse charm, the Teasley 56" five-blade ceiling fan is suitable for a variety of interior settings. Clear seeded bell-shaped glass shades highlights the Graphite finish. Three LED lamps are included, offering energy efficiency and cost savings benefits for the home, while a dual mount canopy accommodates flat or sloped ceilings.

Specifications:

- Galvanized Finish (-141) (plated)
- Steel construction
- Clear seeded Glass Bell
- The Teasley 56" 5-blade ceiling fan is suitable for a variety of interior settings
- Reversible Driftwood and Gray Weathered Wood blades
- Galvanized finish with Brushed Nickel accents
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- Clear seeded bell-shaped glass shades including three 2700K dimmable vintage LED lamps, offering 2400 lumens
- Features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light
- Pull chain is Chrome
- Add an accessory wall or remote control for added convenience
- Ideal for Traditional, Transitional and Farmhouse settings
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet
- Dual mount canopy that accommodates flat or sloped ceilings
- A 1" x 6" downrod is included. Longer accessory downrods can be ordered separately
- Teasley offers energy efficiency and cost savings benefits for the home
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting Yes for outlet box included
- 80" of wire supplied
- Driftwood/Grey Weathered Wood reversible blades, plywood construction
- Chrome pull chain with Black fob
- 12.5 blade pitch
- Triple capacitor speed control, manual reverse control Speed, Manual Reverse
- Airflow: 5749 CFM*
- Energy consumption: 75 watts (excluding lights)*
- Airflow efficiency: 76 cfm/watt*
- * Fan on a downrod

Performance:

Number of Modules	3
Input Power	7w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	2400/114 (LM-79) per module
CCT	2700 K
CRI	80 CRI
Life (hours)	15,000 (L70/TM-21)
Warranty	Limited Lifetime
Labels	ULus Dry location listed

P250004-141

Images:



Dimensions:

 Diameter: 56"
 Height: 22-1/2"

 Glass
 Width: 4-3/4"
 Height: 5-5/8"

P250004-141

Dimming Notes:

P250004 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron DV-603P

Lutron LGCL-153CL

Lutron CT-103P-WH

Leviton 6684

Almond LUXDM600-12

Leviton 6631-LA

Leviton IPI06

Leviton S-600P-WH

Lutron DV-603PR

Lutron S-600PR-WH

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.