

roject:	
ixture Type:	
ocation:	

Loring

Ceiling Mounted • Dry Location Listed

Contact:

Description:

Outfitted with stylish mixed metal elements, this ceiling fan shows off an industrial-inspired, open-cage design. Four plywood blades rotate within the cage and anchor to a vintage-style base. The fan's stunning aesthetic and its handy remote control are ready to help you and your family stay comfortable and relaxed all year round.

Specifications:

- Outfitted with stylish mixed metal elements, this ceiling fan shows off an industrial-inspired, open-cage design.
- Four plywood blades rotate within the cage and anchor to a vintage-style base.
- The fan's stunning aesthetic and its handy remote control are ready to help you and your family stay comfortable and relaxed all year round.
- · Ideal for any living room, great room, or bedroom.
- · Perfect for urban industrial and farmhouse settings.
- Measures 32-7/8-inch width by 15-1/4-inch height.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- Canopy covers a standard 4" recessed outlet box: 7.75 in W., 1.313 in ht., 7.75 in depth
- 80 in of wire supplied

P250006-031



Performance:

Input Voltage	120 V
Input Frequency	60 Hz
Warranty	Limited Lifetime Warranty
Labels	cULus Dry Location Listed
	AC motor

Dimensions:

Diameter: 32-7/8 in Height: 15-1/4 in

