

Alleron

 Ceiling Mounted • Damp Location Listed **PROGRESS LED**

Description:

Alleron Collection 4-Blade Antique Black 56-Inch DC Motor LED Urban Industrial Ceiling Fan

Specifications:

- White Opal Glass Bowl
- Dimmable to 10% brightness
- Canopy covers a standard 4" recessed outlet box: 6.5 in W., 2.5 in ht., 6.5 in depth
- 80 in of wire supplied

Performance:

Number of Modules	1
Input Power	24 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,100
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	cULus Damp Location Listed Meets California Title 24 JA8-2016 DC motor

P250009-182-30



Dimensions:

Diameter: 56 in
Height: 16 in

White Opal Glass Bowl
Width: 8-1/8 in
Height: 2-1/8 in