

Fixture Type:	
Location:	

Royer

Ceiling Mounted • Dry Location Listed

Contact:

Description:

This ceiling fan offers a charming rustic look ideal for farmhouse-style spaces in need of a fresh breeze. Four plywood blades attach to the fixture's center by finely detailed metal arms. The fan's center is coated in a beautiful antique nickel finish to complement your home decor.

Specifications:

- Four plywood blades attach to the fixture's center by finely detailed metal arms.
- The fan's center is coated in a beautiful antique nickel finish to complement your home decor.
- This ceiling fan offers a charming rustic look ideal for farmhouse-style spaces in need of a fresh breeze.
- · Ideal for any living room, great room, or bedroom.
- · Perfect for farmhouse or rustic settings.
- Measures 56-inch width by 17-13/16-inch height.
- · Light kit not included.
- · Remote control included.
- · Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- Canopy covers a standard 4" recessed outlet box: 5.13 in W., 2.19 in ht., 5.13 in depth
- · 80 in of wire supplied

Performance:

Input Voltage	120 V
Input Frequency	60 Hz
Warranty	Limited Lifetime Warranty
Labels	cULus Dry Location Listed
	AC motor

P250010-081





Dimensions:

Diameter: 56 in Height: 17-13/16 in

