

Project:		
Fixture Type:		
Location:		
Contact:		



P250011-141-WB

Midvale

 $\label{eq:midvale} \mbox{Midvale Collection 5-Blade Galvanized 56-Inch AC Motor 2-Light Coastal Ceiling Fan}$

Category: Ceiling Fans

Finish: Galvanized Finish (Painted) **Construction:** Steel Housing

Glass/Shade: White Opal Glass Cylindrical

Length: 56 in Diameter: 56 in Height: 20.85 in

White Opal Glass Cylindrical

Width: 8-1/8 in Height: 6 in

		r icigiit. O iii	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	80 in of wire supplied	Quantity: two 7 W max. ST19 or LED	cULus Damp Location Listed
Canopy covers a standard 4" recessed outlet box: 6.5" W., 2.5"	120 V	equivalent	Limited Lifetime Warranty
ht., 6.5" depth		E26 base Porcelain Socket	