

| DATE:    | TYPE: |  |
|----------|-------|--|
| NAME:    |       |  |
| PROJECT: |       |  |

Diameter: 23-1/2" Length: 23-1/2" Height: 18-1/8"

## P250012-143-22

## Gulliver

Freshen and revitalize your farmhouse or seaside home with the Gulliver ceiling fan. Three Gray Wood bands wrap together to create a statement-making, open-cage design that encloses the blades responsible for creating a reviving, fresh breeze.

- A hand-painted, woodgrain texture complements Rustic and Modern Farmhouse decor and Urban Industrial and Coastal interior settings
- Three-light "fandelier" delivers ultra-powerful, revitalizing cool air movement stylishly packaged in an open cage design
- Dual-toned frame color combines Graphite with weathered gray accents to add rustic charm
- Effortlessly control the full-range dimming and fan speed capabilities with the companying three-speed remote with its batteries included, making it ready for immediate use
- Manual reverse switch for year-round comfort
- Dual-mount canopy that accommodates flat or sloped ceilings
- Measures 23-1/2 in dia X 18-1/8 in ht with 80 in lead wires
- Uses and includes three dimmable, 5-1/2-watt max, medium base vintage LED bulbs
- UL damp location listed
- Limited lifetime warranty included

Category: Ceiling Fans Finish: Graphite

Construction: Steel Construction

| MOUNTING  | ELECTRICAL                                      | LAMPING                      | ADDITIONAL INFORMATION                             |
|---|---|------------------------------|--|
| Ceiling mounted   | Pre-wired                                       | Quantity:                    | cETLus Damp location listed                        |
| Mounting Yes for outlet box included                      | 36" of wire supplied                            | Three 5.5w max.(included)E26 | Limited Lifetime warranty                          |
|   | Triple capacitor speed control,                 | base                         | Airflow: 1297 CFM*                                 |
| Canopy covers a standard 4" octagonal recessed outlet box | manual reverse control Speed,<br>Manual Reverse |                              | Energy consumtion: 39 watts<br>(excluding lights)* |
| 7.3125 W., 2.0625 ht., 7.3125<br>depth                    | 120 V   |                              | Airflow efficiency: 33 cfm/watt*                   |
| асра.   |   |                              | * Fan on a downrod                                 |
|   |   |                              |  |